

RATING:

| | PVC/PET |
|-----------------------|--------------------------|
| DESIGN PRESSURE | .150 PSIG at 140°F/180°F |
| | (1.03 MPa at60°C / 82°C) |
| MIN. OPERATING TEMP | 20°F |
| | (-7°C) |
| FACTORY TEST PRESSURE | CE/ASME |
| | 225PSIG/165 PSIG |
| | (1.55Mpa/1.13 MPa) |
| | |

(6.20 MPa)

INTENDED USE:

The AquaLine 80CF15 Fiberglass Pressure Vessel is designed for continuous, long term use as housing for AquaLine range of micro filtration elements.

The AquaLine 80CF15 is designed in accordance with the engineering standards of the Boiler and Pressure Vessel Code of the American Society of Mechanical Engineers (ASME) as per Section X Edition 2019 and all metallic parts are designed as per Section VIII Division I Edition 2019. At small additional cost vessels can be inspected during construction by an ASME Authorized Inspector and ASME Code stamped.

The AquaLine 80CF15 must be installed, operated and maintained in accordance with the listed precautions and good industrial practice to assure safe operation over a long service life.

The high performance Filament wound FRP shell must be allowed to expand under pressure; undue restraint at support points or piping connections can cause leaks to develop in the shell. This side-ported vessel requires special precautions in mounting and connection to piping so that the vessel will not be subjected to excessive stress due to bending moments acting at the side openings in the fiberglass shell. The end closure, incorporating close fitting, interlocking metal components, must be kept dry and free of corrosion; deterioration can lead to catastrophic mechanical failure of the head.

Pentair will assist the purchaser in determining the suitability of this standard vessel for their specific operating conditions. The final determination however, including evaluation of the standard material of construction for compatibility with the specific corrosive environment, shall be the responsibility of the purchaser. Alternate materials with enhanced corrosion resistance are available on special order.

Specifications are subject to change without notice.

PRECAUTIONS:

- DO...read, understand and follow all instructions; failure to take every precaution will void warranty and may result in vessel failure.
- DO...mount the shell on horizontal members at span "S" using compliant vessel supports furnished; Shim saddles if required. Tighten hold down straps just snug
- DO...align and center side ports with the manifold header. Correct, causes of misalignment in a row of vessels connected to the same header.
- DO...use flexible type IPS grooved-end pipe couplings, or equal, at side ports; allow full, 0.125 inch gap between port and piping, and position piping to maximize flexibility of connection.
- DO...provide flexibility in, and support for piping manifolds so that vessel can grow in length under pressure without undue restraint; provide additional flexible joints in large pipes leading to manifold header.
- DO... Lubricate seals sparingly, using nonpetroleum Based lubricants, i.e. Parker Super O-lube®, Glycerin or suitable silicone based lubricants.
- DO...provide overpressure protection for vessel set at not more than 105% of design pressure.
- DO...inspect end closures regularly; replace components that have deteriorated and correct causes of corrosion.
- DO NOT...work on any component until first verifying that pressure is relieved from vessel.
- DO NOT...make rigid piping connections to ports or clamp vessel in any way that resists growth of fiberglass shell under pressure.
- DO NOT...pressurize vessel until double-checking to verify that the Locking Ring is in place and fully seated.
- DO NOT...operate vessel at pressure and temperature in excess of its rating.
- DO NOT...tolerate leaks or allow end closures to be routinely wetted in any way.
- DO NOT... operate outside the pH range of 3-11.

ORDERING:

Using the chart below, please check the features you require and fax them with your purchase order to our customer service department for further processing.

For optional materials and / or feature not listed below, please consult the factory for pricing and availability.

 VESSEL LENGTH CODE

 MODEL: AquaLine 80CF15-60


 CERTIFICATION REQUIRED

- □ Certified by Pentair with Compliance to ASME Section X Hydro testing at 1.1 times.
- □ ASME code stamped and National Board Registered.
- □ CE Marking.

HEAD ASSEMBLY MATERIAL SELECTION

- □ Standard: For 140'F application, Engineering Thermoplastic components in PVC as per drawing 17036 on First page.
- Option: For 180'F application, Engineering Thermoplastic components in PET as given below. (Please consult factory as these options will affect pricing and vessel lead time).

| | HEAD COMPONENTS FOR 180'F APPLICATION | | | | |
|------------|---------------------------------------|-------|-------------------------------------|--|--|
| DWG REF | QTY | | DESCRIPTION | MATERIAL | |
| 6 | 1 | 17433 | 1/4" FNPT Air Vent Port | SA-479 UNS S32760. | |
| 7 | 2 | 45286 | 1/4" Air Vent Port Seal | O - Ring - EPDM | |
| 8 | 1 | 17179 | Bearing Plate Downstream | SB-221 6061-T6 Aluminium alloy - Hard anodized. | |
| 9 | 1 | 17404 | Sealing Plate Downstream | Engineering Thermoplastic - PET. | |
| 10 | 1 | 17103 | Bearing Plate Upstream | SB-221 6061-T6 Aluminium alloy - Hard anodized. | |
| 11 | 1 | 17453 | Sealing Plate Upstream | Engineering Thermoplastic - PET. | |
| 12 | 1 | 17434 | 3" Product Port | SA-995 CD3MWCuN (J93380) | |
| 13.1 | 1 | 17452 | 3" Product Port Adapter | Engineering Thermoplastic - PET. | |
| 13.2 | 1 | 17435 | Product port holding pin | Engineering Thermoplastic | |
| 14 | 2 | 17164 | 3" Seal for Product Port Adapter | Ethylene Propylene - O - Ring | |
| 15 | 1 | 17127 | 3" Port Retainer Ring | 316 Stainless Steel. | |
| 16 | 2 | 96000 | Head Seal | Ethylene Propylene O - Ring | |
| 17 | 1 | 17128 | Product Port Seal | Ethylene Propylene O - Ring | |
| 18 | 1 | 17104 | Handle Assembly | 316 Stainless Steel | |
| 19 | 1 | 45247 | Plug Retainer Ring | 316L Stainless Steel | |
| 20 | 1 | 17407 | Plug | Engineering Thermoplastic - PET. | |
| 21 | 1 | 45312 | Plug seal | Ethylene Propylene O - Ring | |



| FEED PORT CONFIGURATION | | | ſ |
|-------------------------|--|----------------|---|
| | | PORT SIZE CODE | |
| | | | |

| TOTAL DELL CODE | | |
|-----------------|----------------|--|
| Α | 1" FNPT END | |
| G | 3" GROOVED END | |

Please fill out quantity for each configuration 1A 4G – Standard

- \square 1A 2G (Optional)
- ____ IA2G = (Optional)

1A 2G 4G – (Optional)

For complete information on proper use of the vessel Please refer to the AquaLine User Guide No 97676.

© Pentair.